

Project Name/No:

Item No:


Quantity: SIS#: AIA/CSI#:

# **Free-Standing Ventless Recirculating Hood** Model FSH-2A-99

- Free-standing design allows you to add deep fryers to the cook line without need for expensive building modifications or costly expansion of an existing conventional ventilation system.
- Ductwork to the outside is not necessary. Generally, the FSH-2A-99 can be used where traditional hood solutions are prohibited or do not fit within your budget.
- Designed with more headroom under the hood ... ideal for pressure fryers with hinged lids or fryers equipped with basket lifts.
- Accommodates appliances 10" to 24" wide and fits into spaces with 8-foot ceilings.
- UL listed for use with approved cooking appliances (frvers only) and features Giles' proven 3-stage air cleaning system for capturing & removing grease-laden cooking vapors from the air. Listed to UL-YZCT (Canadian UL-YZCT-7) ... complies with ANSI/UL-710B.
- Hood features a factory installed, self-contained, Ansul® R102 Wet Chemical Fire Suppression System, consisting of Automan release mechanism, 1-1/2 gallon tank, piping, appliance/plenum nozzles, detector link brackets and cable conduit. Customer shall provide for final field installation, set-up, charging & commissioning ... work must be performed by an authorized Ansul® Distributor/Dealer ... not included with purchase.

Design

(ŲL),



ii realures					
	Ventless Cleaning	s Hood 3-Stage Air g:	<ul><li>Standard Features:</li><li>Built-in interlock relay for powering fryer under the hood.</li></ul>		
for a for a star	Stage 1 -	Stainless steel Baffle Filter traps large grease particulate.	<ul> <li>Complete filter set.</li> <li>Built-in fire suppression system.</li> <li><i>PUSH-TO-START</i> switch hood must be manually restarted</li> </ul>		
	Stage 2 -	Sustainable Electronic Air Cleaner (E.A.C.) electrostatically captures & collects fine particulate on fins within the cell.	<ul><li>after any power interruption, in order to power appliance underneath.</li><li>Adjustable leveling legs.</li><li>Exhaust Air Diverter - reduces required ceiling clearance.</li></ul>		
	Stage 3 -	Disposable Charcoal Filter helps to control cooking odors in the recirculated air.	<ul> <li>Optional Features:</li> <li>Interlocked appliance power receptacle installed in the hood stand. 50A max load.</li> </ul>		

#### **IMPORTANT INFORMATION !!**

Orders for GILES Recirculating/Ventless Hood systems will not be accepted until Giles confirms ... 1) Purchaser has received all necessary approvals from local authorities ... 2) the appliance to be used is within the hood's listing limitations ... 3) the Purchaser is aware of specific site requirements & limitations stated in the GFSE Recirculating/Ventless Hood Approval Letter (HAL) which must be complied with during installation. The HAL must be completed, submitted (along with any requested documentation) and approved by Giles before an order is accepted and production is initiated.

The HAL document is available for download at <u>www.gfse.com</u> under the SUPPORT tab in VENTLESS DOCUMENTS.

#### Appliance Limits: IMPORTANT! HOOD LISTED ONLY FOR USE WITH ELECTRICALLY HEATED APPLIANCES ... NO GAS

Hood listed for FRYERS only ... must comform to the following limits:

- Maximum power: 20 kW
- Maximum cooking surface area: 380 sq in [2,452 sq cm]
- Maximum cooking temp: 350°F [177°C] •
- Maximum shortening capacity: 110 lbs [50 kg]
- Fryer width (side to side): 10" [254 mm] to 24" [610 mm] •

#### GILES Food Service Equipment ISO 9001-2015 Registered


PO Box 210247; 2750 Gunter Park Drive W; Montgomery, AL 36109 USA 334.272.1457 • Fax 334.239.4117 • Toll Free 800.554.4537 (US/Canada Only) • www.gfse.com • Email: services@gfse.com

Printed in USA, Form 63776 (Rel. Date: Feb.2006; Rev. Date: Feb.2020, Rev. F)

## Ventless Hood Model FSH-2A-99

Project Name/No:\_\_\_\_\_

Item No:



#### **Specifications**

Construction: 16, 18 & 20-ga. stainless steel ... aluminized steel where applicable

Dimensions:			Electrical Specifications: (Hood Only)				
Width	Depth	Height		Voltage	Ph	lase	Amps
30-7/16" [748 mm]	30-7/16" [748 mm] 40-3/16" [1021 mm] 9		5-47/64" [2432 mm] 208-240		10	or 3	5
Ventless Hood:       • Power cord NOT provided; field wired.         • Exhaust: 510 - 680 CFM       • Approx. Sound Level: 65 dB							
Shipping Specifications: Freight Class 125							
Width Length Height				Cube		Crated Weight	
46" [1168 mm]	106" [2692 mm]	48" [1219 mm	]	135.4 cu ft [3.8	3 cu m]	595 lbs [270 kg]	

Accessory Items Included: Baffle Filter • EAC Filter Cell • Charcoal Filter • (1) Can, Spray Foam EAC Cell Cleaner (sample)

## **IMPORTANT!** Before Ordering

- Purchaser must obtain, read, complete, and submit the Giles Hood Approval Letter (HAL) for approval. By signing the HAL, Purchaser affirms that the intended installation site has been assessed and that it is in compliance with the minimum requirements, stated therein ... kitchen size, ceiling height, fresh outside air supply, room air exchange rate, exhaust ventilation, clearances, etc.
- Verify that fryer to be used is within limits shown on first page ... contact factory to resolve any questions.
- Does available electrical power meet hood specifications?

## How To Specify

 Specify Appliance Opening (X) Oversize 1/8" to 1/4" [3.2 mm - 6.4 mm] for clearance.

✓	Opening Designation	Width (X)	~	Opening Designation	Width (X)
	А	24-1/8 [613]		E	15-5/8 [397]
	В	20-1/8 [511]		F	15-1/8 [384]
	С	18-5/8 [473]		G	14-1/8 [359]
	D	16-1/8 [410]		Н	10-1/8 [257]

## **2** Determine Base Part Number

Choose from the following:

<ul> <li>Image: A start of the start of</li></ul>	Voltage		Ph	Filter Type	Part No.
	208-240	60	3	EAC	71831
	208-240	60	3	HEPA	71832



2750 Gunter Park Drive West • Montgomery, AL 36109 USA 334.272.1457 • Toll Free: 800.554.4537

#### **3** Select Options to be Factory Installed

Add <u>OPTION CODE</u> (or Codes in ascending order) to base part number, e.g. XXXXX-1, XXXXX-5. Standard Hood = only part no..

	<	Code	Description			
		STANDARD - NO OPTIONS				
5 APPLIANCE RECEPTACLE, 3-PH, 50A, N		APPLIANCE RECEPTACLE, 3-PH, 50A, NEMA 15-50R				

### **4** Extra Accessories (sold separately)

$\checkmark$	Qty	Description	Part No.
		Baffle Filter	43200
		E.A.C. Collector Cell	20520
		Charcoal Filter	30248
		Foaming Spray EAC Cleaner (12-ct Case, 20-oz Cans)	41510

## **5** Shipping - Specify shipping method

Giles reserves the right to change specifications and/or product design without notice. Such revisions do not entitle the buyer to corresponding changes, improvements, additions or replacement with respect to previously purchased equipment. Printed in U.S.A. Form 63776 (Rel. Date Feb.2006; Rev. Date Feb.2020; Rev. F)